

# Rittal – The System.

Faster – better – everywhere.



## SV 9344.330

# NH fuse-switch disconnecter

State: 14/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.330 - NH fuse-switch disconnecter with electronic fuse monitoring

## Features

Model No.	SV 9344.330
Design	For mounting plate assembly
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	630 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm
Connection of round conductors	10 - 300 mm <sup>2</sup>
Number of poles	3-pole
with electronic fuse monitoring	Yes
Round conductor cross-section	10 - 300 mm <sup>2</sup>
Packs of	1 pc(s).

# Features

---

Net weight	4.4 kg
Gross weight	4.444 kg
Copper weight (kg per piece)	1.06
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 3, 630 A, 400-690 V, 3-pole, screw M10, with electronic fuse monitoring, for mounting plate assembly

# Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK