

Rittal – The System.

Faster – better – everywhere.



KX 1509.000

Priključna omarica KX, jeklena pločevina, brez plošče z uvodnicami

State: 28.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1509.000 - Priključna omarica KX, jeklena pločevina, brez plošče z uvodnicami

Majhno ohišje KX, priključna omarica KX, brez tesnilne plošče omogoča prilagodljivo notranjo namestitev ob hkratnem ohranjanju visoke stopnje zaščite.



Features

Št. Modela	KX 1509.000
Opis izdelka	Majhno ohišje KX, priključna omarica KX, brez plošče z uvodnicami omogoča prilagodljivo notranjo zasnovano z visoko stopnjo zaščite.
Material	Ohišje: jeklena pločevina Pokrov: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in pokrov: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje s pokrovom Mini odmična ključavnica
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Razred zaščite po IEC 60 529	IP 66

Features

Tipaska ocena po UL 50E	Type 1 Type 3R Type 4 Type 12
IK koda	IK08
Mere	Širina: 500 mm Višina: 300 mm Globina: 120 mm
Debelina materiala - pokrov	1,25 mm
Debelina materiala - ohišje	1,25 mm
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	5,424 kg
Bruto teža	5,57 kg
PCF na paket (od zibelke do vrat)	37,13 kg CO2 eq (Cat B)
Opomba o kategoriji PCF	Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana
Carinska tarifna številka	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	KX Terminal box, WHD: 500x300x120 mm, sheet steel, without mounting plate, with cover, without gland plate

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
-----------	--

Approvals

Certificates

Protection category

Explanations

Manufacturer's declaration

Declaration of conformity

Declaration of conformity UK

PCF-declaration