

# Rittal – The System.

Faster – better – everywhere.



## KX 1511.000

Priključna omarica KX, jeklena pločevina, brez plošče z uvodnicami

State: 11.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1511.000 - Priključna omarica KX, jeklena pločevina, brez plošče z uvodnicami

Majhno ohišje KX, priključna omarica KX, brez tesnilne plošče omogoča prilagodljivo notranjo namestitev ob hkratnem ohranjanju visoke stopnje zaščite.



## Features

Št. Modela	KX 1511.000
Opis izdelka	Majhno ohišje KX, priključna omarica KX, brez plošče z uvodnicami omogoča prilagodljivo notranjo zasnovano z visoko stopnjo zaščite.
Material	Ohišje: jeklena pločevina Pokrov: jeklena pločevina, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Ohišje in pokrov: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje s pokrovom Mini odmična ključavnica
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Razred zaščite po IEC 60 529	IP 66

# Features

---

Tipaska ocena po UL 50E	Type 1 Type 3R Type 4 Type 12
IK koda	IK08
Mere	Širina: 400 mm Višina: 400 mm Globina: 120 mm
Debelina materiala - pokrov	1,25 mm
Debelina materiala - ohišje	1,25 mm
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	5,7 kg
Bruto teža	5,87 kg
PCF na paket (od zibelke do vrat)	26,1 kg CO2 eq (Cat B)
Opomba o kategoriji PCF	Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana
Carinska tarifna številka	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Opis izdelka	KX Terminal box, WHD: 400x400x120 mm, sheet steel, without mounting plate, with cover, without gland plate

# Approvals

---

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
-----------	--

---

# Approvals

---

Certificates

Protection category

---

Explanations

Manufacturer's declaration

Declaration of conformity

Declaration of conformity UK

PCF-declaration