

Rittal – The System.

Faster – better – everywhere.



BG 1584.520

Priključna ohišja BG

State: 24.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1584.520 - Priključna ohišja BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Št. Modela	BG 1584.520
Material	Ohišje: jeklena pločevina Vrata: jeklena pločevina Nadzorno okno: polikarbonat, 4 mm
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje z vrati Nadzorno okno v vratih
Protection category NEMA	NEMA 12
Razred zaščite po IEC 60 529	IP 65
IK koda	IK08
Mere	Širina: 300 mm Višina: 300 mm Globina: 80 mm
Debelina materiala - ohišje	1,25 mm
Debelina materiala - vrata	1,25 mm
Položaj tečajev vrat	left
Število podpornih tirnic	2
Izrezi (količina x premer)	2
Zaklepanje	Različica ključavnice: Ključavnica Število ključavnic: 1 Vložek ključavnice: 3 mm dvojni nastavek

Features

Kabelski vhod (količina x premer)	2 x M12 M20 M25
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	3,075 kg
Bruto teža	3,18 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	BG Bus enclosure, WHD: 300x300x80 mm, Sheet steel, with metric holes in the base and support rail, Door with viewing window, hinged on the left

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity