


# Rittal – The System.

Faster – better – everywhere.



## SG 2371.000

### Flashing light component

State: 29.1.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2371.000 - Flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

## Features

|                                                 |                                                                                                                                                                                                                                                                    |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                                       | SG 2371.000                                                                                                                                                                                                                                                        |
| Design                                          | Flashing light component                                                                                                                                                                                                                                           |
| Product description                             | With 360° signal transmission thanks to optimised prism system.<br>Number of potential stages = 5 components, with identical voltage.                                                                                                                              |
| Benefits                                        | Simple assembly and contact via bayonet fastener.<br>Configuration of up to five components with the same voltage.<br>Components are available in a range of colours and voltages.<br>Flashing and stroboscopic light element incl. lamp, suitable for direct use. |
| Function principle                              | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel                                                                                                                                                |
| Material                                        | Enclosure of polyamide<br>Cap: Transparent polycarbonate                                                                                                                                                                                                           |
| Colour                                          | Red                                                                                                                                                                                                                                                                |
| Diameter                                        | 70 mm                                                                                                                                                                                                                                                              |
| Rated impulse withstand voltage, phase to phase | 2500 V AC                                                                                                                                                                                                                                                          |
| Rated insulation voltage                        | 250 V AC                                                                                                                                                                                                                                                           |
| Rated current max.                              | 125 mA                                                                                                                                                                                                                                                             |
| Dimensions                                      | Height: 56 mm                                                                                                                                                                                                                                                      |
| Protection category to IEC 60 529               | IP 54 if a cover or acoustic component is fitted at the top                                                                                                                                                                                                        |
| Rated operating voltage                         | 24 V (DC)                                                                                                                                                                                                                                                          |
| Packs of                                        | 1 pc(s).                                                                                                                                                                                                                                                           |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 0.09          |
| Gross weight          | 0.098         |
| Customs tariff number | 85311095      |
| EAN                   | 4028177220072 |
| ETIM 9                | EC000232      |
| ETIM 8                | EC000232      |
| ECLASS 8.0            | 27371220      |

# Approvals

|           |                          |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed)<br>UR |
|-----------|--------------------------|