


# Rittal – The System.

Faster – better – everywhere.



## SV 9635.030 Board

State: 10/09/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.030 - Board RiLine Compact

Board with integral busbars.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SV 9635.030  |
| Function principle                  | Shock-hazard-protected busbar board for the safe accommodation and contacting of components, thanks to simple plug-in mounting<br>Pre-punched pitch units in the board allow secure, fast positioning of components<br>Reduces wiring work by contacting directly onto the board |
| Material                            | Polyamide<br>Polycarbonate<br>E-Cu<br>Fire protection corresponding to UL 94   |
| Colour                              | RAL 7035   |
| Supply includes                     | Integral busbars   |
| IP protection category to IEC 60529 | IP 2X  |
| Standards                           | UL 508<br>IEC 61 439   |
| Rated current max.                  | 160 A  |
| Rated operating voltage             | 690 V (AC)<br>600 V (DC)   |
| Note                                | The technical data may vary for UL applications  |
| for mounting plate assembly         | Yes  |
| Number of poles                     | 3-pole   |
| Dimensions                          | Width: 700 mm<br>Height: 160 mm<br>Depth: 45.1 mm  |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 2.75   |

# Features

|                              |               |
|------------------------------|---------------|
| Gross weight                 | 2.86          |
| Copper weight (kg per piece) | 1.57          |
| Customs tariff number        | 85469010      |
| EAN                          | 4028177978423 |
| ETIM 9                       | EC001900      |
| ETIM 8                       | EC001900      |
| ECLASS 8.0                   | 27400613      |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |