

Rittal – The System.

Faster – better – everywhere.



SV 9635.110

Circuit-breaker component adaptor

State: 02/06/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.110 - Circuit-breaker component adaptor 3-pole

For mechanical attachment and direct contacting of circuit-breakers on the board.

Features

| | |
|--------------------------------|--|
| Model No. | SV 9635.110 |
| Function principle | For mechanical attachment and direct contacting of circuit-breakers on the board Circuit-breaker is fitted using variably adjustable fixing points (M4) |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Note | Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor Depending on the circuit-breaker used, there may be a reduction in output The technical data may vary for UL applications |
| Rated current max. | 160 A |
| Rated operating voltage | 600 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Dimensions | Width: 90 mm Height: 160 mm Depth: 45 mm |
| Distance between fixing points | 30 mm |
| Cable outlet | Top/bottom |
| To fit manufacturer (model) | ABB (XT2) Allen Bradley (140G-H) Eaton (NZM1) |
| Packs of | 1 pc(s). |
| Net weight | 0.55 kg |
| Gross weight | 0.588 kg |

Features

| | |
|------------------------------|---|
| Copper weight (kg per piece) | 0.276 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV CB component adaptor 160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 30 mm |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
