Rittal – The System.

Faster - better - everywhere.





HD 2410.031 Cable gland HD

State: 9.12.2025 (Source: rittal.com/si-sl)




HD 2410.031 - Cable gland HD

More compact design and the lock nut is included with the supply.







Features

Model No.	HD 2410.031
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of
	harmful micro-organisms.
	Much easier, and therefore cheaper to clean compared with
	conventional cable glands.
Applications	Manufacturer
	Clean room technology (e.g. pharmaceuticals)
	Biotechnology
	Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303)
	Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M25 x 1.5
For cable diameters	12 - 17 mm
Operating temperature range	-20 °C100 °C

© Rittal 2025

Features

IP protection category to IEC 60 529	IP69 / IPX8 (5 bar, 30 min)
Type rating to UL 50E	Type 1
	Type 2
	Type 4
	Type 4X
	Type 12
	Type 12K
	Type 13
Packs of	5 pc(s).
Net weight	0.545
Gross weight	0.548
Customs tariff number	73072980
EAN	4028177928695
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UL + C-UL (listed)
	VDE

© Rittal 2025 3