

Rittal – The System.

Faster – better – everywhere.



SV 9676.749 Connection plate

State: 03/06/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.749 - Connection plate for laminated copper bars

For the connection of laminated flat copper bars.

Features

| | |
|---|---|
| Model No. | SV 9676.749 |
| Product description | For connecting laminated copper bars to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness. |
| Material | Connection plate: E-Cu Thrust piece: Stainless steel Busbar claw: Stainless steel |
| Supply includes | Assembly parts (excluding screws) |
| Assembly instruction | The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply. Busbar claw with threaded insert M10 |
| Bars per conductor | 2 |
| Mounting dimensions | 50 mm |
| Clamping area for laminated copper bars (W x H) | 100 x 20 mm |
| To fit laminated copper bars | Qty.: 2 with no. of membranes: 10 with membrane width: 100 mm with membrane thickness: 1 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.62 kg |
| Gross weight | 0.639 kg |
| Copper weight (kg per piece) | 0.27 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002270 |
| ECLASS 8.0 | 27400613 |

Features

Product description

SV Connection plate, clamping area WH: 100x20 mm, (Flat-PLS)

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK