## Rittal – The System.

Faster - better - everywhere.





# SZ 2500.200 LED system light

State: 2.11.2025 (Source: rittal.com/si-sl)



## SZ 2500.200 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.





#### **Features**

Model No.	SZ 2500.200
Design	Without socket
Benefits	Optimum illumination of the entire enclosure
	Optionally with clip, screw and magnetic attachment  A configuration to suit every application
	<u> </u>
Design	Without socket
	90° rotating connector
	Adjustable light distribution
Material	Light body: Extruded aluminium
	Light cover: Polycarbonate
	Light ends: PC-ABS
Colour	Enclosure: RAL 7016
Supply includes	Assembly screws
Power consumption	11 W
Connection options	Infeed, 3-pole
	Through-wiring, 3-pole
	Door-operated switch
Overvoltage category	II

© Rittal 2025

### Features

Protection class	II (all-insulated)
Light – installation type	Screw-fastening
	Clip attachment
	Magnetic attachment (accessory)
Rated impulse withstand voltage, phase to earth	2500 V AC
Rated insulation voltage	300 V AC
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	900 lm
Light colour	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm
	Height: 75 mm
	Depth: 23 mm
Operating temperature range	-20 °C55 °C
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz
IP protection category to IEC 60 529	IP 20
Packs of	1 pc(s).
Net weight	0.426
Gross weight	0.56
Customs tariff number	94054990
EAN	4028177806955
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

© Rittal 2025 3

## Approvals

Approvals	cqc-ccc
	ENEC
	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 4