

Rittal – The System.

Faster – better – everywhere.



SV 9677.865 Current transformer

State: 10/12/2025 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.865 - Current transformer

For inductive measurement of current flow.

Features

Model No.	SV 9677.865
Product description	Compact design without altering the installation depth via mechanical integration into the top-mounting components (185 mm centre-to-centre spacing); this allows space-saving assembly.
Material	Polyamide
For size	1 - 3
To fit Model No.	9677.100 9677.110 9677.115 9677.200 9677.210 9677.215 9677.300 9677.310 9677.315 9677.340 9677.770 9677.780 9677.900
Rated power input	2.5 VA
Type of electrical connection	Box terminal
Insulation material (class)	H
Primary current	250 A
Secondary current	5 A
Accuracy Class	1

Features

Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
--------------------	--

Connection of round conductors	2.5 - 4 mm ²
--------------------------------	-------------------------

Rated frequency	50 - 60 Hz
-----------------	------------

Packs of	1 pc(s).
----------	----------

Net weight	0.13
------------	------

Gross weight	0.16
--------------	------

Customs tariff number	85044085
-----------------------	----------

EAN	4028177971554
-----	---------------

ETIM 9	EC002048
--------	----------

ECLASS 8.0	27141146
------------	----------
