

# Rittal – The System.

Faster – better – everywhere.



## SK 3138.000

## Roof-mounted fan, roof vent

State: 5.4.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3138.000 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.



## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SK 3138.000  |
| Design                              | roof-mounted   |
| Product description                 | Roof-mounted fan with a high protection category and flexible installation from the inside or outside. |
| Colour                              | RAL 7035   |
| Supply includes                     | Complete unit ready to install, including pleated filter   |
| Fan                                 | without fan motor  |
| Dimensions                          | Width: 400 mm<br>Height: 133 mm<br>Depth: 400 mm   |
| Installation depth                  | 27,5 mm  |
| Mounting cut-out                    | Cut-out width: 258 mm<br>Cut-out depth: 258 mm   |
| IP protection category to IEC 60529 | IP 21 without filter mat<br>IP 54 including pleated filter   |

# Features

---

|                             |  |
|-----------------------------|--|
| Protection category NEMA    | NEMA 12  |
| Note                        | A chopped-fibre filter filter may optionally be used to increase the protection category to IP 55 (see accessories).<br>To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| Operating temperature range | -20 °C...55 °C   |
| Storage temperature range   | -40 °C...70 °C   |
| Packs of                    | 1 pc(s).   |
| Net weight                  | 3,2 kg   |
| Gross weight                | 3,5 kg   |
| Customs tariff number       | 84145915   |
| ETIM 9                      | EC000320   |
| ETIM 8                      | EC000320   |
| ECLASS 8.0                  | 27180716   |
| Product description         | SK roof-mounted fan, roof vent, WHD: 400 x 133 x 400 mm, without fan motor   |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | CSA<br>UL + C-UL - FTTA<br>UR + C-UR (recognized)         |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

Roof-mounted fan, roof vent

SK 3138.000

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories.

Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.

Colour: RAL 7035

Supply includes: Complete unit ready to install, including pleated filter

Fan: without fan motor

Dimensions (WxHxD): 400x133x400 mm

Mounting cut-out (WxD): 258x258 mm

Installation depth: 27.5 mm

IP protection category to IEC 60 529:

IP21 without filter mat, IP54 including pleated filter

Protection category NEMA: NEMA 12

Operating temperature range: -20 °C to 55 °C

Storage temperature range: -40 °C to 70 °C

Weight/pack: 3.2 kg