

Rittal – The System.

Faster – better – everywhere.



SK 3165.830

Ventilator za namestitev na vrata

State: 12.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SK 3165.830 - Ventilator za namestitvev na vrata

For mounting on tubular door frames of server racks (front or rear door) and to support the horizontal air routing of the IT equipment.

Features

Št. Modela	SK 3165.830
Prednosti	Z dodajanjem dveh razširitvenih kompletov ventilatorjev se pretok zraka poveča na 1200 m ³ /h. Smer zračnega pretoka zraka se enostavno spremeni z vrtenjem ventilatorja. Več enot je mogoče razporediti v kaskadno razporeditev. Enostavna montaža na cevni okvir vrat. Popolnoma ožičeno, pripravljeno za priklop
Barva	RAL 7035
Obseg dobave	2 ventilatorja Priključni kabel (2,5 m) Sestavni deli
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
Poraba energije Pel	Pri 50 Hz: 70 W Pri 60 Hz: 70 W
Maks. nazivni tok	Pri 50 Hz: 0,38 A Pri 60 Hz: 0,36 A
Mere	Širina: 693 mm Višina: 606 mm Globina: 64,5 mm
Opomba	Samo za namestitvev na cevni okvir vrat!
Stopnja hrupa	55 dB(A)
Primerno za	Vrsta ohišja: Server enclosures TS 8 DK-TS Širina: 800 mm
Delovno temperaturno območje	20 °C...55 °C
Paketi	1 pc(s).

Features

Neto teža	11,523 kg
Bruto teža	12,129 kg
Carinska tarifna številka	73269098
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Opis izdelka	SK Door-mounted fan, for horizontal air routing, for mounting on the tubular door frame, To fit enclosure width: 800 mm, WHD: 693x606x64,5 mm