

Rittal – The System.

Faster – better – everywhere.



SK 3201.960

Toroidni transformator

State: 25.5.2026 (Source: [rittal.com/si-si](https://www.rittal.com/si-si))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.960 - Toroidni transformator Primarni priključek 115 V/400 V

Za napajanje stenskih toplotnih izmenjevalnikov zrak/voda 230 V. Na voljo s primarnim priključkom 115 V ali 400 V.

Features

Št. Modela	SK 3201.960
Opis izdelka	Za napajanje stenskih toplotnih izmenjevalnikov zrak/voda v izvedbah 230 V. Na voljo s primarnim priključkom 115 V ali 400 V.
Tehnični podatki	Izhod 110 VA Toleranca napetosti $\pm 10\%$ Primarni priključek dolžine 3500 mm Sekundarni priključek dolžine 1500 mm Za namestitev na 35 mm nosilno letev EN 50 022
Obseg dobave	Toroidni transformator Sestavni deli
Paketi	1 pc(s).
Snap-mounting to support rails TS 35	Yes
Za model št.	3363.X0X 3364.X0X 3212.230 3214.100 3214.700 3215.100 3215.700
Mere	Širina: 105 mm Višina: 123 mm Globina: 55 mm
Nazivna delovna napetost	230 V (secondary), 1~, 50 Hz/60 Hz 400 V (primary), 2~, 50 Hz/60 Hz
Neto teža	2,2 kg

Features

Bruto teža	3,214 kg
Carinska tarifna številka	85043121
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Opis izdelka	SK Toroidal transformer, 400 V (primary), 2~, 50/60 Hz, 230 V (secondary), 1~, 50/60 Hz, WHD: 105 x 123 x 55 mm

Approvals

Explanations

Declaration of conformity