

Rittal – The System.

Faster – better – everywhere.



HD 1318.600

Kompaktno ohišje HD, dvojna vrata

State: 9.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 1318.600 - Kompaktno ohišje HD, dvojna vrata

Ohišja, prilagojena zahtevam industrije hrane in pijače. Nagnjena streha za 30° naprej. Modra barva tesnila za dobro razlikovanje od živil.



Features

| | |
|------------------------------|--|
| Št. Modela | HD 1318.600 |
| Zasnova | Hygienic Design ohišje |
| Opis izdelka | Naklon strehe 30° naprej |
| Material | Ohišje in vrata: nerjavno jeklo 1.4301 (AISI 304) Montažna plošča: jeklena pločevina Vložek ključavnice HD: nerjavno jeklo 1.4404 (AISI 316L) Tesnilo: silikon, v skladu s smernicami FDA 21 CFR 177.2600 |
| Površinska obdelava | Ohišje in vrata: brušena površina, zrnatost 400, hrapavost površine < 0,8 µm Montažna plošča: pocinkana Tesnilo: Modro, barvano (RAL 5010) |
| Obseg dobave | Popolnoma zaprto ohišje Vrata z vstavljenim tesnilom Montažna plošča |
| Mere | Širina: 1.010 mm Višina, spredaj: 1.050 mm Višina zadaj: 1.280 mm Globina: 400 mm |
| Mere montažne plošče (Š x V) | 945 mm x 975 mm |

Features

| | |
|---------------------------------|--|
| Kot odpiranja vrat | 125° |
| IK koda | IK08 |
| Osnovni material | Stainless steel 1.4301 (AISI 304) |
| IP razred zaščite po IEC 60 529 | IP 66 IP X9 |
| Protection category NEMA | NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13 |
| Tipška ocena po UL 50E | Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13 |
| Paketi | 1 pc(s). |
| Neto teža | 80 kg |
| Bruto teža | 82 kg |
| Carinska tarifna številka | 94032080 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | HD Compact enclosure, WHD 1010x1050(D1)x1280(D2)x400 mm, stainless steel 1.4301, with mounting plate, with hinged door and silicone seal |

Approvals

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK

PCF-declaration