## Rittal – The System.

Faster – better – everywhere.





# KX 1566.000 Terminal box KX

State: 15.11.2025 (Source: rittal.com/si-sl)



#### KX 1566.000 - Terminal box KX Stainless steel

The stainless steel terminal box KX delivers maximum data quality and consistency of engineering while ensuring flexibility and reliability across a wide range of applications.







#### **Features**

and consistency of engineering while ensuring flexibility and reliability across a wide range of applications.  Material Enclosure: Stainless steel 1.4301 (AISI 304)		
and consistency of engineering while ensuring flexibility and reliability across a wide range of applications.  Material Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in Pt Surface finish Enclosure and cover: Brushed, grain 180  Supply includes Enclosure with cover Quick-release fastener including plastic bushes  Protection category NEMA NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 4X NEMA 12	Model No.	KX 1566.000
Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU  Surface finish Enclosure and cover: Brushed, grain 180  Supply includes Enclosure with cover Quick-release fastener including plastic bushes  Protection category NEMA NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12	Product description	
Supply includes  Enclosure with cover Quick-release fastener including plastic bushes  Protection category NEMA  NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4 NEMA 4X NEMA 12	Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea
Quick-release fastener including plastic bushes  Protection category NEMA  NEMA 1  NEMA 3R  NEMA 3RX  NEMA 4  NEMA 4X  NEMA 12	Surface finish	Enclosure and cover: Brushed, grain 180
NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12	Supply includes	
Protection category to IEC 60 529 IP 66	Protection category NEMA	NEMA 3R NEMA 3RX NEMA 4 NEMA 4X
	Protection category to IEC 60 529	IP 66

© Rittal 2025

### Features

Type rating to UL 50E	Type 1
	Type 3R
	Type 3RX
	Type 4
	Type 4X
	Type 12
Dimensions	Width: 300 mm
	Height: 200 mm
	Depth: 120 mm
Material thickness - cover	1,25 mm
Material thickness - enclosure	1,25 mm
Lock	Number of locks: 4
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	2.7
Gross weight	2.866
Customs tariff number	84879059
EAN	4028177919204
E-Number Sweden	E3465232
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

## Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3

#### Tender text

Enclosure (terminal box, stainless steel)

Enclosure with cover:

Stable stainless steel design, body folded from a single piece and welded, with protection channel all-round cover opening, Solid rear panel with knockouts, cover with foamed-in PU seal, with PE conductor connection in the enclosure, earthing in the cover via bolt, for quick and easy earthing, with quick-release fastener.

QR code:

QR code printed on body, cover and rating plate for clear identification and easy retrieval of relevant product information and documentation, and for clear traceability of the individual parts. Accessories: Cover hinge, mounting plate, top hat rail, wall mounting bracket, mounting claw for second mounting level.

Material:

Enclosure, cover: Stainless steel 1.4301 (AISI 304)

Surface finish: Brushed, grain size 180 Protection category to IEC 60 529: IP 66 Protection category to UL 508A: Type 4X Dimensions (W x H x D): 300x200x120 mm

© Rittal 2025 4