


Rittal – The System.

Faster – better – everywhere.



SZ 2370.570

Komponenta utripajoče LED luči

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2370.570 - Komponenta utripajoče LED luči za signalni steber, modularno

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

Features

Št. Modela	SZ 2370.570
Zasnova	Komponenta utripajoče LED luči
Prednosti	Enostavna montaža in kontakt z bajonetnim pritrdilnim elementom. Konfiguracija do petih komponent z enako napetostjo. Komponente so na voljo v različnih barvah in napetostih. Utripajoč in stroboskopski svetlobni element z žarnico, primeren za neposredno uporabo.
Način delovanja	Možna je modularna postavitvev s priključki, optičnimi in akustičnimi komponentami, žarnicami z žarilno nitko in napisno ploščo
Material	Ohišje iz poliamida Pokrovček: prozoren polikarbonat
Barva	Rumena
Premer	70 mm
Nazivna impulzna vzdržna napetost, med fazami	2500 V AC
Nazivna izolacijska napetost	250 V AC
Mere	Višina: 56 mm
Razred zaščite po IEC 60 529	IP 54 if a cover or acoustic component is fitted at the top
Nazivna delovna napetost	230 V
Paketi	1 pc(s).
Neto teža	0,07 kg
Bruto teža	0,084 kg
Carinska tarifna številka	94054990

Features

ECLASS 8.0	27371220
------------	----------

Opis izdelka	SZ LED flashing light component, for signal pillar, modular, 230 V, amber
--------------	---

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------