


Rittal – The System.

Faster – better – everywhere.



SM 2384.030

Switch housings

State: 21.1.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.030 - Switch housings Stainless steel

Switch housing made from stainless steel 1.4301 (AISI 304) with switch cut-outs, diameter: 22.5 mm. Protection category IP 66.

Features

Model No.	SM 2384.030
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Enclosure and cover: Brushed, grain 240
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 220 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1,25 mm
Material thickness - enclosure	1,25 mm
Pitch pattern	60 mm
Cut-outs (quantity x diameter)	3 x 22.5 mm
Lock	Lock version: Quick-release fastener including plastic bushes Number of locks: 4
Cable entry (quantity x diameter)	3
No. of metric knockouts	3
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	1.1

Features

Gross weight 1.226

Customs tariff number 94039910

EAN 4028177529434

ETIM 9 EC000261

ETIM 8 EC000261

ECLASS 8.0 27180101

Approvals

Explanations Declaration of conformity
Declaration of conformity UK