

Rittal – The System.

Faster – better – everywhere.



HD 2410.031

Kabelska uvodnica HD

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 2410.031 - Kabelska uvodnica HD

Priložena bolj kompaktna zasnova in varovalna matica.



Features

Št. Modela	HD 2410.031
Zasnova	Standardne
Opis izdelka	Kompaktnejša zasnova in varovalna matica sta že vključeni v obseg dobave.
Prednosti	Gladke, trdne zunanje površine učinkovito preprečujejo nabiranje škodljivih mikroorganizmov. Veliko lažje in zato cenejše čiščenje v primerjavi z običajnimi kabelskimi uvodnicami.
Aplikacije	Proizvajalec Tehnologija čistih prostorov (npr. farmacevtska industrija) Biotehnologija Kemična industrija
Material	Matica: nerjavno jeklo 1.4305 (AISI 303) Tesnilo: EPDM, skladno s FDA 21 CFR 177.2600
Obseg dobave	Blokirna matica
Mere	Navoj: M25 x 1.5

Features

Za kable s premerom	12 - 17 mm
Delovno temperaturno območje	-20 °C...100 °C
IP razred zaščite po IEC 60 529	IP69 / IPX8 (5 bar, 30 min)
Tipska ocena po UL 50E	Type 1 Type 2 Type 4 Type 4X Type 12 Type 12K Type 13
Paketi	5 pc(s).
Neto teža	0,545 kg
Bruto teža	0,548 kg
Carinska tarifna številka	73072980
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	HD Cable gland, stainless steel 1.4305, size: M25x1,5, for cables Ø 12-17 mm, Standard version

Approvals

Approvals	UL + C-UL (listed) VDE
-----------	---------------------------