

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2411.851**

**Kabelska uvodnica, medenina**

State: 7.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.851 - Kabelska uvodnica, medenina

Integrirane vpenjalne membrane zagotavljajo zanesljivo privijanje in razbremenitev napetosti za zaščito kablov.

## Features

Št. Modela	SZ 2411.851
Prednosti	Ker se uvodnice in varovalna matica prodajajo skupaj v enem paketu, to prihrani dodatno naročanje in shranjevanje. Vpenjalne membrane za enakomerno zategovanje in razbremenitev napetosti za zaščito kablov
Material	Medenina Tesnilo: CR/NBR
Površinska obdelava	nikljano
IP razred zaščite po IEC 60 529	IP 68 (5 bar, 30 min)
Mere	Višina: 43 mm
Navoj	M40 x 1.5
Dolžina navoja	9 mm
Min. premer kabla	19 mm
Maks. premer kabla	28 mm
Delovno temperaturno območje	-40 °C...100 °C
torque	17 Nm
Širina med ploščami	43 mm
Mere	Navoj: M40 x 1.5 Dolžina navoja: 9 mm
Tipska ocena po UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Paketi	4 pc(s).

## Features

---

Neto teža	0,64 kg
Bruto teža	0,692 kg
Carinska tarifna številka	74198090
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Opis izdelka	SZ Cable gland, brass, size: M40x1,5, for cables ø 19-28 mm

## Approvals

---

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK