# Rittal – The System.

Faster – better – everywhere.





# SZ 2500.100 LED system light

State: 6.11.2025 (Source: rittal.com/si-sl)



## SZ 2500.100 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.





#### **Features**

| Model No.          | SZ 2500.100   |
|--------------------|---|
| Design             | Without socket                                      |
| Benefits           | Optimum illumination of the entire enclosure        |
|                    | Optionally with clip, screw and magnetic attachment |
|                    | A configuration to suit every application           |
| Design             | Without socket                                      |
| Material           | Light body: Extruded aluminium                      |
|                    | Light cover: Polycarbonate                          |
|                    | Light ends: PC-ABS                                  |
| Colour             | Enclosure: RAL 7016                                 |
| Supply includes    | Assembly screws                                     |
| Power consumption  | 5 W   |
| Connection options | Infeed, 2-pole                                      |
|                    | Through-wiring, 2-pole                              |
|                    | Door-operated switch                                |
| Protection class   | II (all-insulated)                                  |
|                    |   |

© Rittal 2025

### Features

| Light – installation type               | Screw-fastening   |
|---|---|
|   | Clip attachment   |
|   | Magnetic attachment (accessory)                                     |
| Installation options                    | The internal mounting rail AX and the mounting bracket are required |
|   | when installing in compact enclosures                               |
| Luminous flux                           | 400 lm  |
| Light colour                            | 4000 K (neutral white)  |
| Note                                    | Connection accessories should be ordered separately                 |
| Dimensions                              | Width: 262 mm   |
|   | Height: 55 mm   |
|   | Depth: 23 mm  |
| Operating temperature range             | -20 °C55 °C   |
| Rated operating voltage                 | 100 V - 230 V, 1~, 50 Hz/60 Hz                                      |
| IP protection category to IEC 60<br>529 | IP 20   |
| Packs of                                | 1 pc(s).  |
| Net weight                              | 0.213   |
| Gross weight                            | 0.28  |
| Customs tariff number                   | 94054990  |
| EAN                                     | 4028177806931   |
| E-Number Sweden                         | E3465308  |
| ETIM 9                                  | EC000321  |
| ETIM 8                                  | EC000321  |
| ECLASS 8.0                              | 27189241  |
|   |   |

# Approvals

| Approvals |
|-----------|
|-----------|

© Rittal 2025 3

# **Approvals**

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025