

# Rittal – The System.

Faster – better – everywhere.



## SV 3433.010

# Bus-mounting fuse base

State: 2.4.2026 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3433.010 - Bus-mounting fuse base

3-pole, for 60 mm bar centre distance.

## Features

Model No.	SV 3433.010
Material	Bus-mounting fuse base: Fibreglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to-centre spacing	60 mm
Type of electrical connection	Box terminal
Fuse inserts	D III-E 33 (adaptor screw)
Rated insulation voltage $U_i$	690 V
Rated current max.	63 A
Rated operating voltage	690 V (DC) 690 V, 3~
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 57 mm Height: 209 mm
Connection of round conductors	1.5 - 25 mm <sup>2</sup>
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole
Rated operating voltage (L1 + L2)	690 V (DC)
Rated operating voltage (L1 + L3)	690 V (DC)
Round conductor cross-section	1.5 - 25 mm <sup>2</sup>

## Features

---

Packs of	10 pc(s).
Net weight	3 kg
Gross weight	3,18 kg
Copper weight (kg per piece)	0,071
Customs tariff number	85369095
ETIM 9	EC001644
ETIM 8	EC001644
ECLASS 8.0	27142120
Product description	SV Bus-mounting fuse base, DIII-E33, 63 A, 690 V, 3-pole, round conductor connection 1,5-25 mm <sup>2</sup> , adaptor screw

## Approvals

---

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity