
Rittal – The System.

Faster - better - everywhere.





SV 3454.500 Conductor connection clamp

State: 4.11.2025 (Source: rittal.com/si-sl)



SV 3454.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

SV 3454.500
For connecting round conductors and laminated copper bars.
Sheet steel
Zinc-plated, passivated
22.5 x 20 mm
Wire end ferrules should be used with fine wire conductors
70 - 185 mm²
5 mm
15 pc(s).
1.95
1.982
7.6 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
85369010
4028177042711
EC000001
EC000001
27141146

© Rittal 2025

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

Tender text

SV conductor connection clamps

for E-CU busbars and Rittal PLS.

for bar thickness: 5 mm

Connection of round conductors 70 - 185 mm2

Wire end ferrules should be used with

fine wire conductors.

Clamping area: for laminated

copper bars 22.5 x 20 mm

Tightening torque

Conductor connection clamp: 12 - 15 Nm

Material: sheet steel, zinc plated, passivated

© Rittal 2025