

Rittal – The System.

Faster – better – everywhere.



AS 4050.817

Strojni navojni sveder

State: 15.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.817 - Strojni navojni sveder

Strojni navojni rezalniki za obdelovalne centre Perforex BC, rezkalne terminale Perforex Milling Terminals MT S in laserske centre LC.

Features

Št. Modela	AS 4050.817
Zasnova	HSSE-V3 Uparjeno Za navojno luknjo Form B s spiralno konico Visokozmogljivo jeklo z vanadijem
Opis izdelka	Orodje za izdelavo navojev za obdelovalni center Perforex BC, rezkalni terminal Perforex MT in laserski center LC.
Mere	Navoj: M12
Obdelovalni material	Steel Stainless steel Aluminium Plastic
Paketi	3 pc(s).
Neto teža	0,18 kg
Bruto teža	0,182 kg
Carinska tarifna številka	82051000
ETIM 9	EC002155
ETIM 8	EC002155
ECLASS 8.0	36609208
Opis izdelka	Machine thread tap M12, packs of 3