

Rittal – The System.

Faster – better – everywhere.



AS 4055.070

**Ročni hidravlični komplet
prebijalnikov, M16 - M63**

State: 10.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.070 - Ročni hidravlični komplet prebijalnikov, M16 - M63

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

Features

Št. Modela	AS 4055.070
Zasnova	Ta komplet vključuje standardne luknjače od M16 do M63
Prednosti	Podaljšajte življenjsko dobo orodja z vgrajenim nadtlačnim ventilom Luknjači, hidravlični luknjači in pribor za izdelavo okroglih, kvadratnih in pravokotnih izrezov v jeklu in nerjavnem jeklu
Obseg dobave	Ročni hidravlični prebijač, raven 7 luknjačev z razdelilnikom, tridelno Hidravlični vijak Ø 19 mm Hidravlični vijak Ø 9,5 / 19 mm Pilotni sveder HSS Ø 10 mm Komplet distančnih tulcev (3-delni) Plastični kovček
Obdelovalni material	Sheet steel
Največja debelina obdelovalnega materiala, jeklena pločevina	2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø prebijača	16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm 50,5 mm 63,5 mm

Features

Za navoje	M16 M20 M25 M32 M40 M50 M63
Paketi	1 pc(s).
Neto teža	5,3 kg
Bruto teža	5,34 kg
Carinska tarifna številka	82034000
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046
Opis izdelka	Hand hydraulic punch set straight M16,20,25,32,40,50,63 mm
