



AS 4055.150

Luknjač z razdelilnikom, okrogel

State: 9.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.150 - Luknjač z razdelilnikom, okrogel za nerjavno jeklo, tridelno, okroglo

Za izrezovanje okroglih izrezov.

Features

Št. Modela	AS 4055.150
Zasnova	Tridelni
Obseg dobave	Ženske matrice Moške matrice
Obdelovalni material	Stainless steel
Največja debelina obdelovalnega materiala, nerjavno jeklo	2,5 mm
Ø prebijača	50,5 mm
Za navoje	M50
Opomba	Pri delu s ključi je treba uporabiti napenjalne vijake s krogličnimi ležaji
Suitable for hydraulic bolt order number	4055.663
Napenjalni vijak (Ø x D)	19 x 75 mm
Ø hidravličnega napenjalnega vijaka	19 mm
Paketi	1 pc(s).
Neto teža	0,657 kg
Bruto teža	0,731 kg
Carinska tarifna številka	82073010
ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047

Features

Opis izdelka

Splitter hole punch, round for stainless steel, round, with triple splitting