

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.581

# Komplet luknjačev z razdelilnikom, M12 do M40

State: 2.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.581 - Komplet luknjačev z razdelilnikom, M12 do M40 za jekleno pločevino, tridelno

Za izrezovanje okroglih izrezov.

## Features

|  |  |
|--|--|
| Št. Modela   | AS 4055.581  |
| Zasnova  | Tridelni   |
| Obseg dobave   | 6 ženskih matric<br>6 moških matric<br>Napenjalni vijak s krogličnim ležajem Ø 6 x 40 mm<br>Napenjalni vijak s krogličnim ležajem Ø 9,5 x 50 mm<br>Napenjalni vijak s krogličnim ležajem Ø 19 x 55 mm<br>Pilotni sveder HSS Ø 10 mm<br>1 pločevinka maziva za podmazovanje<br>Plastični kovček |
| Obdelovalni material   | Sheet steel  |
| Največja debelina obdelovalnega materiala, jeklena pločevina | 1,5 mm<br>2 mm<br>2 mm<br>2 mm<br>3 mm<br>3 mm   |
| Ø prebijača  | 12,5 mm<br>16,2 mm<br>20,4 mm<br>25,4 mm<br>32,5 mm<br>40,5 mm   |
| Za navoje  | M12<br>M16<br>M20<br>M25<br>M32<br>M40   |

# Features

|  |   |
|--|---|
| Opomba                                   | Pri delu s ključi je treba uporabiti napenjalne vijake s krogličnimi ležaji |
| Suitable for hydraulic bolt order number | 4055.660<br>4055.661<br>4055.661<br>4055.661<br>4055.663<br>4055.663        |
| Paketi                                   | 1 pc(s).  |
| Neto teža                                | 2,2 kg  |
| Bruto teža                               | 2,256 kg  |
| Carinska tarifna številka                | 82073010  |
| ETIM 9                                   | EC002121  |
| ETIM 8                                   | EC002121  |
| ECLASS 8.0                               | 21044719  |
| Opis izdelka                             | Splitter hole punch set, M12 to M40 for sheet steel, with triple splitting  |