

Rittal – The System.

Faster – better – everywhere.



AS 4055.581

Komplet luknjačev z razdelilnikom, M12 do M40

State: 11.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.581 - Komplet luknjačev z razdelilnikom, M12 do M40 za jekleno pločevino, tridelno

Za izrezovanje okroglih izrezov.

Features

Št. Modela	AS 4055.581
Zasnova	Tridelni
Obseg dobave	6 ženskih matric 6 moških matric Napenjalni vijak s krogličnim ležajem Ø 6 x 40 mm Napenjalni vijak s krogličnim ležajem Ø 9,5 x 50 mm Napenjalni vijak s krogličnim ležajem Ø 19 x 55 mm Pilotni sveder HSS Ø 10 mm 1 pločevinka maziva za podmazovanje Plastični kovček
Obdelovalni material	Sheet steel
Največja debelina obdelovalnega materiala, jeklena pločevina	1,5 mm 2 mm 2 mm 2 mm 3 mm 3 mm
Ø prebijača	12,5 mm 16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm
Za navoje	M12 M16 M20 M25 M32 M40

Features

Opomba	Pri delu s ključi je treba uporabiti napenjalne vijake s krogličnimi ležaji
Suitable for hydraulic bolt order number	4055.660 4055.661 4055.661 4055.661 4055.663 4055.663
Paketi	1 pc(s).
Neto teža	2,2 kg
Bruto teža	2,256 kg
Carinska tarifna številka	82073010
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21044719
Opis izdelka	Splitter hole punch set, M12 to M40 for sheet steel, with triple splitting