Rittal – The System.

Faster – better – everywhere.





SZ 4140.820 LED compact system light

State: 23.11.2025 (Source: rittal.com/si-sl)



SZ 4140.820 - LED compact system light

Supply voltage: 24 V DC







Features

| Model No. | SZ 4140.820 |
|--------------------------|--|
| Benefits | Max. EMC capacity. |
| | Safe, thanks to operation in the extra-low safety voltage range. |
| | Economical energy use. |
| | Low-maintenance thanks to the use of LEDs. |
| | May be connected to a door-operated switch. |
| Function principle | Integral through-wiring. |
| | Universal attachment options. |
| | Vertically hinged light cone |
| Material | Light body: Extruded aluminium |
| | Light cover: Polycarbonate (halogen-free) |
| | Light ends: PC-ABS |
| Colour | Similar to RAL 7035 |
| Supply includes | LED compact system light |
| | Light |
| | Light cover |
| | Assembly parts |
| Mounting distance screws | 350 mm |

© Rittal 2025

Features

| Connection options | Power supply via connectors Door-operated switch Through-wiring (creating rows of lights) |
|---|--|
| Light | LEDs, cold white |
| Protection class | III (SELV) |
| Switch (type) | Integral on/off/door-operated switch |
| Light cover | Yes |
| Light – installation type | Screw-fastening Clip attachment Magnetic attachment (accessory) |
| Rated impulse withstand voltage, phase to earth | Depending on the power pack |
| Rated impulse withstand voltage, phase to phase | Depending on the power pack |
| Rated insulation voltage | Depending on the power pack |
| Rated current max DC note | When configuring rows of lights, the maximum rated current is 2 amperes |
| With DC | 0,08 A |
| Number of LEDs | 20 |
| Mounting distance clip/magnet | 275 mm |
| Installation options | Directly onto the enclosure section with 25 mm pitch pattern Via mounting kit magnet AE: with rail for interior installation |
| Note | Only intended for use in enclosures and sealed cases When using on customer-supplied power packs, it is important to obtain the requisite approvals depending on the application When configuring rows of lights, the maximum rated current is 2 amperes |
| Light cone adjustment | Yes |
| Dimensions | Width: 330 mm Height: 32.8 mm Depth: 20.64 mm |

© Rittal 2025 3

Features

| Rated operating voltage | 24 V (DC) |
|---|---------------|
| IP protection category to IEC 60 529 | IP 20 |
| Packs of | 1 pc(s). |
| Net weight | 0.29 |
| Gross weight | 0.296 |
| Customs tariff number | 94054990 |
| EAN | 4028177630130 |
| E-Number Sweden | E4302506 |
| ETIM 9 | EC000321 |
| ETIM 8 | EC000321 |
| ECLASS 8.0 | 27189241 |

Approvals

| Explanations | Declaration of conformity |
|--------------|------------------------------|
| | Declaration of conformity UK |

© Rittal 2025