

# Rittal – The System.

Faster – better – everywhere.



## SK 3239.724 Blue e+ filter fan

State: 1.12.2025 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3239.724 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput 20 – 1,160 m<sup>3</sup>/h, protection category IP 54 as standard.



## Features

Model No.	SK 3239.724
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Benefits	<ul style="list-style-type: none"><li>Maximum air throughput via pleated filter included in the delivered state</li><li>Easy filter changes, thanks to a new opening mechanism on the louvred grille</li><li>Faster installation on the enclosure with optimised detent hooks</li><li>Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability</li><li>Tool-free assembly</li></ul>
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Axial, DC motor

# Features

Air throughput, unimpeded airflow (with chopped-fibre filter)	With DC: 100 m <sup>3</sup> /h
Air throughput, unimpeded airflow (with pleated filter)	With DC: 110 m <sup>3</sup> /h
Air throughput with matching outlet filter including chopped-fibre filter	With DC: 75 m <sup>3</sup> /h
Air throughput with matching outlet filter including pleated filter	With DC: 92 m <sup>3</sup> /h
Rated operating voltage	24 V (DC)
Power consumption Pel	With DC: 5.7 W
Rated current max.	With DC: 0.27 A
Dimensions	Width: 204 mm Height: 204 mm Depth: 105 mm
Installation depth	84 mm
Mounting cut-out	Cut-out width: 177 mm Cut-out height: 177 mm
IP protection category to IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used
Operating temperature range	-15 °C...55 °C
Storage temperature range	-30 °C...70 °C
Noise level	With DC: 51 dB(A)
Packs of	1 pc(s).

# Features

---

Net weight	0.78
Gross weight	0.989
Customs tariff number	84145915
EAN	4028177998179
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

---

Approvals	30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity