


Rittal – The System.

Faster – better – everywhere.



CM 5110.500

Kompaktna sistemska ohišja CM

State: 2.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CM 5110.500 - Kompaktna sistemska ohišja CM

Enclosure with door of sheet steel, with mounting plate and open base to accommodate base plates. Protection category IP 55. A symbiosis of the enclosure benefits of Rittal compact enclosures, and the configuration diversity of the TS 8 baying enclosure system. Perforated mounting strips in the door for fast attachment of support strips, cable conduit holders and covers.



Features

Št. Modela	CM 5110.500
Material	Ohišje: jeklena pločevina 1,5 mm Vrata: jeklena pločevina, 2,0 mm, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih 3-točkovni sistem zaklepanja z dvojnimi vložki Montažna plošča Odprto podnožje za individualen vhod kablov
Razred zaščite NEMA	NEMA 12 with selection of the appropriate gland plates or trim panel
Razred zaščite po IEC 60 529	IP 55 with selection of the appropriate gland plates or trim panel
IK koda	IK08

Features

Mere	Širina: 600 mm Višina: 800 mm Globina: 400 mm
Mere montažne plošče (Š x V)	540 mm x 755 mm
Število vrat	1
Zamenljiv tečaj vrat	Yes
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	36,05 kg
Bruto teža	38,1 kg
Carinska tarifna številka	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Opis izdelka	CM Compact system enclosure, WHD: 600x800x400 mm, Sheet steel, with mounting plate, single-door, open base

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK