

# Rittal – The System.

Faster – better – everywhere.



## SK 3240.300 Blue e+ outlet filter

State: 8.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.300 - Blue e+ outlet filter

The outlet filter is used in conjunction with the corresponding fan-and-filter unit to dissipate heat loss from enclosures, ventilate the enclosure and protect temperature-sensitive components. This is achieved through the direct infeed of ambient air, the temperature of which must be lower than the permissible internal temperature of the enclosure.



## Features

|                  |  |
|------------------|--|
| Model No.        | SK 3240.300  |
| Design           | wall-mounted   |
| Benefits         | Easy filter changes, thanks to a new opening mechanism on the louvred grille<br>Faster installation on the enclosure with optimised detent hooks<br>Tool-free assembly |
| Material         | Plastic  |
| Colour           | RAL 7035   |
| Supply includes  | Outlet filter<br>Pleated filter  |
| Mounting cut-out | Cut-out width: 224 mm<br>Cut-out height: 224 mm  |
| To fit Model No. | SK 3240.7xx/3240.9xx/3241.7xx/3241.9xx   |
| Dimensions       | Width: 255 mm<br>Height: 255 mm<br>Depth: 45.2 mm  |

## Features

|                                     |  |
|-------------------------------------|--|
| Protection category NEMA            | Type 12 with chopped-fibre filter/pleated filter<br>Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood                                 |
| IP protection category to IEC 60529 | IP 54 with chopped-fibre filter/pleated filter<br>IP 55 with pleated filter and absorber mat<br>IP 56 with chopped-fibre filter/pleated filter and hose-proof hood |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 0.4  |
| Gross weight                        | 0.67   |
| Customs tariff number               | 39269097   |
| EAN                                 | 4028177998360  |
| ETIM 9                              | EC002513   |
| ETIM 8                              | EC002513   |
| ECLASS 8.0                          | 27180706   |

## Approvals

|           |  |
|-----------|--|
| Approvals | UL + C-UL - FTTA<br>UR + C-UR (recognized) |
|-----------|--|