


Rittal – The System.

Faster – better – everywhere.



SK 3243.300 Blue e+ izhodni filter

State: 11.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3243.300 - Blue e+ izhodni filter

Za prezračevanje s konvekcijo je mogoče v zgornji in spodnji del ohišja namestiti izhodni filter.



Features

Št. Modela	SK 3243.300
Zasnova	stenska namestitev
Prednosti	Enostavna menjava filtra zaradi novega mehanizma odpiranja na lamelni rešetki Hitrejša namestitev na ohišje z optimiziranimi zaskočnimi zatiči Sestavljanje brez orodja
Material	Plastika
Barva	RAL 7035
Obseg dobave	Izhodni filter Naguban filter
Izrez za montažo	Širina izreza: 292 mm Višina izreza: 292 mm
Za model št.	SK 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx
Mere	Širina: 323 mm Višina: 323 mm Globina: 44,7 mm
Razred zaščite NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood

Features

IP razred zaščite po IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Paketi	1 pc(s).
Neto teža	0,956 kg
Bruto teža	0,956 kg
Carinska tarifna številka	39269097
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Opis izdelka	SK Blue e+ outlet filter, for fan-and-filter units 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx, WxH 323 x 323 mm, RAL 7035

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--