

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.885

# Zračne pregrade za montažne okvirje TS IT 482,6 mm (19")

State: 28.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.885 - Zračne pregrade za montažne okvirje TS IT 482,6 mm (19")

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

Št. Modela	DK 5501.885
Aplikacije	Za ločevanje vročih/hladnih con znotraj ohišja s predelnimi stenami ali z uporabo LCP sistema.
Material	Jeklena pločevina Polnilna plošča: plastika, UL 94-HB, brez halogenov Krtačni trak: plastika, UL 94-HB
Površinska obdelava	lakirano
Barva	RAL 9005
Obseg dobave	2 navpični obrobi 2 vodoravni obrobi 4 krtačni trakovi Sestavni deli 2 polnilni plošči, 3 U
Navodila za sestavljanje	Navpične in vodoravne obrobe s krtačnim trakom je mogoče namestiti na sprednji in zadnji 482,6 mm (19") montažni okvir za pregrado.
Primerno za	Širina: 800 mm Višina: 1.800 mm
Paketi	1 pc(s).

# Features

---

Neto teža	5,5 kg
Bruto teža	6 kg
Carinska tarifna številka	73269098
ETIM 9	EC000331
ECLASS 8.0	27189272
Opis izdelka	DK Air baffle plate, WxH: 800x1800 mm, For TS IT 482.6 mm (19") mounting frames