

# Rittal – The System.

Faster – better – everywhere.



## DK 5502.010

## Montažna plošča ventilatorja

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5502.010 - Montažna plošča ventilatorja za VX IT, TS IT, TX CableNet

For active ventilation of the VX IT, TS IT or TE 8000, depending on the version.

## Features

Št. Modela	DK 5502.010
Aplikacije	Za uporabo v izrezu, integriranem v strešno ploščo
Barva	RAL 7035
Obseg dobave	1 ventilatorska enota 2 ventilatorja 1 termostat Priključni kabel, odprt Sestavni deli
Pretok zraka na ventilator (neoviran pretok zraka)	160/180
Nazivna delovna napetost	230 V, 1~, 50 Hz/60 Hz
Mere	Širina: 200 mm Višina: 59 mm Globina: 550 mm
Pretok zraka ventilatorjev (neoviran pretok zraka)	1514
Možnosti namestitve	V VX IT s Š x G (mm): 600 x 600 / 600 x 800 / 600 x 1000 / 600 x 1200 / 800 x 600 TS IT s Š x G: 600 x 600 / 600 x 800 / 600 x 1000 / 600 x 1200 / 800 x 600
Opomba	Navedena stopnja hrupa se nanaša na prvi ventilator Priklop prek razdelilne omarice ali priključka, specifičnega za državo
Stopnja hrupa na ventilator	37 dB(A)
Primerno za	Vrsta ohišja: VX IT TS IT TX CableNet

# Features

---

Delovno temperaturno območje	5 °C...55 °C
Paketi	1 pc(s).
Neto teža	3,027 kg
Bruto teža	3,3 kg
Carinska tarifna številka	84149000
ECLASS 8.0	27189272
Opis izdelka	DK Fan mounting plate, for use in the roof plate, incl. 2 fans, may be expanded to up to 3 fans max., WHD: 200x59x550 mm

# Approvals

---

Explanations	Declaration of conformity UK
--------------	------------------------------