

Rittal – The System.

Faster – better – everywhere.



SK 3304.140

Wall-mounted cooling units

State: 19.12.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3304.140 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.

Features

Model No.	SK 3304.140
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1,000 W Cooling output L35 L35/60 Hz: 1,060 W Cooling output L35 L50/50 Hz: 790 W Cooling output L35 L50/60 Hz: 840 W
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Rated current max.	At 50 Hz: 2.8 A At 60 Hz: 2.9 A
Start-up current max.	At 50 Hz: 11.5 A At 60 Hz: 12.7 A
Air throughput (unimpeded air flow)	External circuit: 900 m³/h Internal circuit: 600 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.4
Design	wall-mounted
Dimensions	Width: 400 mm Height: 950 mm Depth: 260 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54

Features

Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.5 kg
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 700 W Power consumption L35 L35/60 Hz: 675 W Power consumption L35 L50/50 Hz: 785 W Power consumption L35 L50/60 Hz: 800 W
Pre-fuse	Motor circuit-breaker: 6.3...10 A
Packs of	1 pc(s).
Net weight	47.501
Gross weight	50.001
Customs tariff number	84158200
EAN	4028177322912
ECLASS 8.0	27180704

Approvals

Approvals	UL + C-UL (listed)
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Wall-mounted cooling units Rittal TopTherm PLUS
with RiNano coating and integral condensate evaporation
Useful cooling output to DIN 3168 L35 L35 1000/1060 W
Rated operating voltage 400 V, 3~, 50 Hz -
460 V, 3~, 60 Hz
Power consumption Pel to DIN 3168 L35 L35 700/675 W
Dimensions W x H x D [mm] 400 x 950 x 260
Refrigerant R 134 a
Temperature range 20°C to 55°C (Setting range +30°C to +55°C)
Temperature control and monitoring via
basic controller with floating fault signal
contact and connection for door operated
switch
Factory setting 35°C
Connection via pluggable terminal strip
Protection category to EN 60 529/10.91
External circuit IP 34/Internal circuit IP 54
Weight 40 kg
Colour RAL 7035