

Rittal – The System.

Faster – better – everywhere.



SK 3311.040 Priključna cev

State: 12.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.040 - Priključna cev

Gibljava priključna cev, ki jo je mogoče skrajšati, vključno z maticami na obeh straneh za priklop LCP/LCU na obstoječe cevovode.

Features

Št. Modela	SK 3311.040
Opis izdelka	Komplet za priklop vode omogoča enostaven priklop hladilne vode LCP na fiksni cevovod na lokaciji.
Material	NBR (notranji) z jekleno spiralo in tkaninskim vložkom
Zasnova	Rack cooling
Dolžina	1,8 m
Priključki za vodo	G 1½" internal thread
Delovno temperaturno območje	-30 °C...70 °C
Dovoljen delovni tlak (p maks.)	16 bar
Paketi	2 pc(s).
Neto teža	6,302 kg
Bruto teža	6,779 kg
Carinska tarifna številka	39173200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Opis izdelka	SK connection hose, for water connection at the top and bottom, for LCP rack/Inline CW, L: 1800 mm