

Rittal – The System.

Faster – better – everywhere.



DK 5505.790

Omrežno/strežniško ohišje TS IT

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5505.790 - Omrežno/strežniško ohišje TS IT s steklenimi vrati, IP 55, prazno ohišje

TS IT, sealed, for direct enclosure-specific climate control. Available without 482.6 mm (19") interior installation as an empty enclosure for individual configuration in a range of size variants, and with a protection category of up to IP 55.

Features

| | |
|------------------------------------|--|
| Št. Modela | DK 5505.790 |
| Material | Jeklena pločevina Aluminij |
| Površinska obdelava | Okvir ohišja: temeljni premaz Notranja montaža: temeljni premaz Vrata in streha: temeljni premaz, prašno barvano |
| General colour | RAL 7035 |
| Barva | Okvir in plošče ohišja: RAL 7035 |
| Obseg dobave | Okvir ohišja TS 8 z vrati in strešno ploščo Steklena aluminijasta vrata spredaj (180°) Vrata iz jeklene pločevine na zadnji strani, 180° tečaji Ključavnica spredaj in zadaj: udoben ročaj za profilne polcilindre in varnostno ključavnico 3524 E Strešna plošča, enodelna, zaprta Talna plošča s kabelskimi uvodnicami, večdelna, zaprta Komplet tesnil in tesnil za plošče z uvodnicami (priloženo) Priključni pribor za izenačevanje potencialov z ozemljitveno točko (priloženo) 12 x 482,6 mm (19") pritrdilni element, 1 U, prevodno (priloženo) 50 Torx vijakov, prevodnih (priloženo) IPPC paleta |
| Mere | Širina: 800 mm Višina: 1.800 mm Globina: 800 mm |
| Design doors | Zatesnjeno, IP 55 |
| Različica s 482,6 mm (19") nivojem | Brez 482,6 mm (19") notranje namestitve |

Features

| | |
|------------------------------|--|
| Razred zaščite po IEC 60 529 | IP 55 only in conjunction with baying seal or screw-fastened side panels |
| Opomba | Glede na to, kako in kje so vrata nameščena, se lahko kot odpiranja vrat razlikuje za izbrane aplikacije. Za ohišja z višino in globino 2000 x 1200 mm / 2200 x 1000 mm / 2200 x 1200 mm so na voljo ustrezne stranske plošče, ki so ob dobavi nameščene na ohišju. |
| Osnovni material | Aluminium |
| Paketi | 1 pc(s). |
| Neto teža | 97,66 kg |
| Bruto teža | 102,8 kg |
| Carinska tarifna številka | 94032080 |
| ETIM 9 | EC002499 |
| ECLASS 8.0 | 27180207 |
| Opis izdelka | TS IT, without 482.6 mm (19") interior installation, glazed door, WHD: 800 x 1800 x 800 mm, 38 U, IP 55 |

Approvals

| | |
|--------------|---------------------------------------|
| Approvals | UL + C-UL (listed) |
| Certificates | Surface finish Protection category |
| Explanations | Declaration of conformity |