

# Rittal – The System.

Faster – better – everywhere.



## DK 5513.790

# Omrežno/strežniško ohišje TS IT

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5513.790 - Omrežno/strežniško ohišje TS IT s steklenimi vrati, IP 55, prazno ohišje

TS IT, sealed, for direct enclosure-specific climate control. Available without 482.6 mm (19") interior installation as an empty enclosure for individual configuration in a range of size variants, and with a protection category of up to IP 55.

## Features

Št. Modela	DK 5513.790
Material	Jeklena pločevina Aluminij
Površinska obdelava	Okvir ohišja: temeljni premaz Notranja montaža: temeljni premaz Vrata in streha: temeljni premaz, prašno barvano
General colour	RAL 7035
Barva	Okvir in plošče ohišja: RAL 7035
Obseg dobave	Okvir ohišja TS 8 z vrati in strešno ploščo Steklena aluminijasta vrata spredaj (180°) Vrata iz jeklene pločevine na zadnji strani, 180° tečaji Ključavnica spredaj in zadaj: udoben ročaj za profilne polcilindre in varnostno ključavnico 3524 E Strešna plošča, enodelna, zaprta Talna plošča s kabelskimi uvodnicami, večdelna, zaprta Komplet tesnil in tesnil za plošče z uvodnicami (priloženo) Priključni pribor za izenačevanje potencialov z ozemljitveno točko (priloženo) 12 x 482,6 mm (19") pritrdilni element, 1 U, prevodno (priloženo) 50 Torx vijakov, prevodnih (priloženo) IPPC paleta
Mere	Širina: 600 mm Višina: 2.200 mm Globina: 1.000 mm
Design doors	Zatesnjeno, IP 55
Različica s 482,6 mm (19") nivojem	Brez 482,6 mm (19") notranje namestitve

# Features

Razred zaščite po IEC 60 529	IP 55 only in conjunction with baying seal or screw-fastened side panels
Opomba	Glede na to, kako in kje so vrata nameščena, se lahko kot odpiranja vrat razlikuje za izbrane aplikacije. Za ohišja z višino in globino 2000 x 1200 mm / 2200 x 1000 mm / 2200 x 1200 mm so na voljo ustrezne stranske plošče, ki so ob dobavi nameščene na ohišju.
Osnovni material	Aluminium
Paketi	1 pc(s).
Neto teža	87,3 kg
Bruto teža	99 kg
Carinska tarifna številka	94032080
ETIM 9	EC002499
ECLASS 8.0	27180207
Opis izdelka	TS IT, without 482.6 mm (19") interior installation, glazed door, WHD: 600 x 2200 x 1000 mm, 47 U, IP 55

# Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish Protection category
Explanations	Declaration of conformity