


# Rittal – The System.

Faster – better – everywhere.



## SE 5852.500

## Sistem samostojećih ohišij SE 8

State: 5.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SE 5852.500 - Sistem samostojećih ohišij SE 8 Nerjavno jeklo

Enclosure widths ranging from 600 to 1200 mm Time-saving assembly work due to the roll-formed side panels



## Features

|                     |   |
|---------------------|---|
| Št. Modela          | SE 5852.500   |
| Material            | Ohišje: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm, brušena zunanost<br>Vrata: nerjavno jeklo 1.4301 (AISI 304), 2,0 mm, brušena zunanost<br>Zadnja plošča: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm, brušena zunanost<br>Plošče z uvodnicami: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm<br>Montažna plošča: jeklena pločevina, 3,0 mm |
| Površinska obdelava | Ohišje, vrata in zadnja plošča: brušeno, zrnatost 400<br>Plošče z uvodnicami: brez premaza<br>Montažna plošča: pocinkana  |
| Obseg dobave        | Ohišje, zaprt zgornji del in stranice<br>Vrata<br>Zapiranje vrat pri enokrilnih ohišjih, možnost zamenjave na nasprotno stran<br>Zadnja plošča, snemljiva<br>Montažna plošča<br>Kabelske uvodnice<br>Ključavnica: 3 mm dvojna ključavnica<br>2 luknjani tirnici TS 18 x 38 mm   |
| Mere                | Širina: 800 mm<br>Višina: 1.800 mm<br>Globina: 500 mm   |

# Features

|                              |  |
|------------------------------|--|
| Mere montažne plošče (Š x V) | 699 mm x 1.696 mm  |
| Razred zaščite po IEC 60 529 | IP 55  |
| Razred zaščite NEMA          | NEMA 12<br>NEMA 3R   |
| IK koda                      | IK10   |
| Število vrat                 | 1  |
| Opomba                       | Zaradi trdote materiala priporočamo uporabo kovinskih torx vijakov za notranjo namestitvev.                                    |
| Osnovni material             | Stainless steel  |
| Paketi                       | 1 pc(s).   |
| Neto teža                    | 122,8 kg   |
| Bruto teža                   | 125,8 kg   |
| Carinska tarifna številka    | 94032080   |
| ECLASS 8.0                   | 27180101   |
| Opis izdelka                 | SE Free-standing enclosure system, WHD: 800x1800x500 mm, Stainless steel 1.4301, with mounting plate, single door at the front |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |