

Rittal – The System.

Faster – better – everywhere.



SE 5854.500

Sistem samostojećih ohišij SE 8

State: 6.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 5854.500 - Sistem samostojećih ohišij SE 8 Nerjavno jeklo

Enclosure widths ranging from 600 to 1200 mm Time-saving assembly work due to the roll-formed side panels



Features

Št. Modela	SE 5854.500
Material	Ohišje: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm, brušena zunanost Vrata: nerjavno jeklo 1.4301 (AISI 304), 2,0 mm, brušena zunanost Zadnja plošča: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm, brušena zunanost Plošče z uvodnicami: nerjavno jeklo 1.4301 (AISI 304), 1,5 mm Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Ohišje, vrata in zadnja plošča: brušeno, zrnatost 400 Plošče z uvodnicami: brez premaza Montažna plošča: pocinkana
Obseg dobave	Ohišje, zaprt zgornji del in stranice Vrata Zapiranje vrat pri enokrilnih ohišjih, možnost zamenjave na nasprotno stran Zadnja plošča, snemljiva Montažna plošča Kabelske uvodnice Ključavnica: 3 mm dvojna ključavnica 2 luknjani tirnici TS 18 x 38 mm
Mere	Širina: 1.000 mm Višina: 1.800 mm Globina: 400 mm

Features

Mere montažne plošče (Š x V)	899 mm x 1.696 mm
Razred zaščite po IEC 60 529	IP 55
Razred zaščite NEMA	NEMA 12 NEMA 3R
IK koda	IK10
Število vrat	1
Opomba	Zaradi trdote materiala priporočamo uporabo kovinskih torx vijakov za notranjo namestitvev.
Osnovni material	Stainless steel
Paketi	1 pc(s).
Neto teža	133 kg
Bruto teža	140,4 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	SE Free-standing enclosure system, WHD: 1000x1800x400 mm, Stainless steel 1.4301, with mounting plate, single door at the front

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK