Rittal – The System.

Faster - better - everywhere.





CP 6380.400 Optipanel

State: 14.12.2025 (Source: rittal.com/si-sl)



CP 6380.400 - Optipanel

Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Super-slimline design, needs hardly more space than the installed equipment itself.







Features

Model No.	CP 6380.400
Design	Support arm connection, rectangular 120 x 65 mm
Benefits	Aluminium enclosure, high thermal conductivity for optimum
	passive heat dissipation.
	Low weight coupled with high stability
	Compatible with all Rittal stand and support arm systems
Material	Enclosure: Extruded aluminium section
	Corner pieces: Die-cast zinc
	Corner protectors: Plastic
General colour	Natural anodised
Colour	Enclosure: Natural anodised
	Corner pieces: RAL 7035
	Corner protectors: similar to RAL 7024
Supply includes	Enclosure with hinged rear panel
	Seals
	Seals and assembly parts for front panels

© Rittal 2025

Features

Dimensions	Width: 564 mm
	Height: 444 mm
	Depth: 110 mm
Installation depth	100 mm
IP protection category to IEC 60 529	IP 65
To fit front panel width	520 mm
To fit front panel height	400 mm
Design	Servicing access from the rear
Note	The support arm connection may be swapped over by rotating the
	enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock
	inserts, plastic handles and T handles, type C
	Hinging of the rear panel on the longest enclosure side
Basic material	Aluminium
Lock	Lock version: Cam
	Number of locks: 2
	Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	7.755
Gross weight	8.163
Customs tariff number	94032080
EAN	4028177663152
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals UL + C-UL (listed)

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025