

# Rittal – The System.

Faster – better – everywhere.



## IW 6901.100

# Industrijske delovne postaje

State: 23.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IW 6901.100 - Industrijske delovne postaje

Lower enclosure based on TS 8 for Industrial Workstations.

## Features

Št. Modela	IW 6901.100
Zasnova	Delovna plošča, predal za tipkovnico, okrasna vrata, zadnja vrata
Material	Ohišje, predal za tipkovnico, okrasna vrata in zadnja vrata: jeklena pločevina Delovna plošča: iverna plošča (plastika - laminirano na obeh straneh (rob))
Površinska obdelava	Ohišje: temeljni premaz, prašno barvna zunanost, teksturirana barva
Barva	Ohišje, delovna plošča: RAL 7035 Robna letev delovne plošče: RAL 7015
Obseg dobave	Ohišje s stranskimi ploščami, pritrjenimi z vijaki od znotraj, podnožje s ploščo z uvodnicami in nivelirnimi nogami Delovna plošča, predal za tipkovnico, okrasna vrata, zadnja vrata Delovna plošča, Š x V x G 610 x 38 x 645 mm
Mere	Širina: 600 mm Višina: 1.000 mm Globina: 645 mm
IP razred zaščite po IEC 60 529	IP 54
Razred zaščite NEMA	NEMA 12
Paketi	1 pc(s).
Neto teža	88,464 kg
Bruto teža	91,2 kg
Carinska tarifna številka	94032080
ETIM 9	EC002502
ECLASS 8.0	27180501

# Features

---

Opis izdelka

IW Industrial workstation, housing, WHD: 600x1000x600 mm, with worktop, keyboard drawer, Designer door at the front, rear door

# Approvals

---

Explanations

Declaration of conformity