

Rittal – The System.

Faster – better – everywhere.



DK 7010.120

Senzorji

State: 2.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.120 - Senzorji for CMC III, PDU, LCP, IoT interface

The temperature/humidity sensor monitors the ambient temperature and air humidity in the enclosure.

Features

Št. Modela	DK 7010.120
Zasnova	Temperature/humidity sensor
Prednosti	Hitra povezava in samodejno zaznavanje s funkcijo plug & play Napajanje se omogoči s povezavo z vmesnikom CAN-BUS.
Aplikacije	Nadzor ohišij v IT, industriji in upravljanju objektov Nadzor ohišij, prostorov in zabojnikov v IT okolju
Način delovanja	The temperature/humidity sensor monitors the ambient temperature and air humidity in the enclosure. Senzor ima vgrajen temperaturni senzor in vgrajen senzor vlažnosti zraka. Nastavitve je mogoče izvesti prek procesne enote CMC III ali IoT vmesnika
Material	Plastika
Površinska obdelava	Spredaj: gladko Ohišje: teksturirano
Barva	RAL 9005
Obseg dobave	Senzor Montažna plošča Sestavni deli
Povezava s CAN vodilom	Direct
Vmesniki	2 x RJ45 CAN bus
Mere	Širina: 80 mm Višina: 30 mm Globina: 40 mm
Delovno temperaturno območje	0 °C...55 °C

Features

Vlažnost okolice (brez kondenzacije)	5...95 %
Paketi	1 pc(s).
Neto teža	0,093 kg
Bruto teža	0,145 kg
Carinska tarifna številka	90269000
ETIM 9	EC002627
Opis izdelka	DK Temperature/humidity sensor, connection via CAN bus interface, WxHxD: 80x30x40 mm, RAL 9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity