




Rittal – The System.

Faster – better – everywhere.




SV 3584.020 CUPONAL busbars

State: 9.2.2026 (Source: rittal.com/si-sl)



SV 3584.020 - CUPONAL busbars

Copper-coated aluminium busbar



Features

Model No.	SV 3584.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2.400 mm
Rated current max.	328 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	30 mm x 5 mm
Dimensions	Length: 2,400 mm
Packs of	6 pc(s).
Net weight	8.52
Gross weight	9
Copper weight (kg per piece)	0.52

Features

Customs tariff number 74071000

EAN 4028177686571

ETIM 9 EC001522

ETIM 8 EC001522

ECLASS 8.0 27370303

Approvals

Explanations Declaration of conformity
Declaration of conformity UK