

# Rittal – The System.

Faster – better – everywhere.



## SV 3585.020 CUPONAL busbars

State: 21.6.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3585.020 - CUPONAL busbars

Copper-coated aluminium busbar

## Features

Model No.	SV 3585.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2.400 mm
Rated current max.	363 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	Flat copper bar width: 20 mm Flat copper bar thickness: 10 mm
Packs of	3 pc(s).
Weight/pack	19,5 kg
Copper weight (kg per piece)	0.7
Customs tariff number	74071000
EAN	4028177686564
ETIM 7.0	EC001522
ECLASS 8.0	27370303

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK