

Rittal – The System.

Faster – better – everywhere.



AS 4050.060 Vpenjalni okvir

State: 25.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.060 - Vpenjalni okvir

Vzporedna obdelava ohišij na obdelovalnih centrih Perforex BC in rezkalnih terminalih Perforex MT za krajše čase priprave in večjo produktivnost.

Features

Št. Modela	AS 4050.060
Zasnova	Pnevmatska vpenjalna naprava
Opis izdelka	Omogoča vzporedno obdelavo ohišij na obdelovalnem centru Perforex BC in rezkalnem terminalu Perforex MT.
Possible number of terminal Boxes for parallel processing	3
Opomba	Uporaba vpenjalnega okvirja (model št. 4050.080) v BC obdelovalnem centru (model št. 4050.230) je možna samo pri različici z dvema vratoma.
Za model št.	4050.101 4055.910 4055.911
Suitable for	Perforex BC 1001 HS Perforex MT 1101 Perforex MT 1101 S
Mere vpenjalnih ohišij maks.	Širina: 200 mm Višina: 300 mm Globina: 300 mm
Mere vpenjalnih ohišij min.	Širina: 85 mm Višina: 70 mm Globina: 70 mm
Paketi	1 pc(s).
Neto teža	25 kg
Bruto teža	25 kg
Carinska tarifna številka	84669360
ETIM 9	EC003010

Features

ETIM 8	EC003010
ECLASS 8.0	36609190
Opis izdelka	AS Multiple fastening, BC 1001, Clamping frame for several small enclosures, - 3 clamping positions in the frame, - Pneumatic clamping device, - Min. enclosure dimensions (W x H x D): 85 x 70 x 70 mm
