## Rittal - The System.

Faster – better – everywhere.





# DK 7480.035 Energy-Box, 482.6 mm (19")

State: 14.12.2025 (Source: rittal.com/si-sl)



# DK 7480.035 - Energy-Box, 482.6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1-3, maximum accommodation of 22 items of installed equipment.

## **Features**

Model No.	DK 7480.035	
Product description	Depth-variable top hat rail for installed equipment to DIN 43 880 in sizes 1 – 3, e.g. to accommodate flush-type socket outlets, circuit-breakers, etc., with cable clamping at the rear and one N and one PE rail each on an insulated base/plinth.	
Colour	RAL 7035	
Supply includes	Energy-Box with depth-variable top hat rail for installed equipment to DIN 43880, sizes 1 – 3, with brush strip for cable entry at the rear Plastic hood including extension cover (UL94-V0) 44 connection clamps, 4 mm² 2 connection clamps, 16 mm² 2 blanking covers 12 clips for strain relief of the connection cables Identification strips, self-adhesive	
Max. pitch units @ 18 mm	22	
Note	Individual population with circuit-breakers at the factory available on request.	
Dimensions	Width: 482.6 mm Height: 132.5 mm Depth: 155 mm	
Units	3 U	
Packs of	1 pc(s).	
Net weight	2.354	
Gross weight	2.54	
Customs tariff number	85366990	
	4028177166004	

© Rittal 2025 2

### **Features**

E-Number Sweden	E7239593	
ETIM 9	EC002620	
ECLASS 8.0	27189261	

#### Tender text

Energy-Box, 3 U,

with adjustable top-hat rail for installed equipment as per DIN 43880 in sizes 1 - 3. A cable clamp is integrated in the box. One N and one PE rails are already fitted on isolated bases. The plastic cover, which includes an extension cover (UL 94-V0), can hold a maximum of 22 pieces of installed equipment (width = 18 mm).

Supply includes:

1 pcs. Energy-Box with depth adjustable top hat rail for installation equipment to DIN 43880, sizes 1-3, maximum 22 HP, including mounted N-and PE-rail on isolated base.

Within a brush strip on the backside for cable entry

1 pcs. plastic hood incl. extension cover (UL-94-V0)

44 pcs. connection clamps, 4 mm<sup>2</sup>

2 pcs. connection clamps, 16 mm<sup>2</sup>

2 pcs. blanking cover

12 pcs. clips for cable strain relief

Identificationstrips, self-adhesive

© Rittal 2025 3