

Rittal – The System.

Faster – better – everywhere.



AS 4050.061 Vpenjalni okvir

State: 31.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.061 - Vpenjalni okvir

Vzporedna obdelava ohišij na obdelovalnih centrih Perforex BC in rezkalnih terminalih Perforex MT za krajše čase priprave in večjo produktivnost.

Features

Št. Modela	AS 4050.061
Zasnova	Pnevmatska vpenjalna naprava
Opis izdelka	Omogoča vzporedno obdelavo ohišij na obdelovalnem centru Perforex BC in rezkalnem terminalu Perforex MT.
Possible number of terminal Boxes for parallel processing	4
Opomba	Uporaba vpenjalnega okvirja (model št. 4050.080) v BC obdelovalnem centru (model št. 4050.230) je možna samo pri različici z dvema vratoma.
Za model št.	4050.107 4050.108 4050.230 4055.920 4055.921 4055.925 4055.926
Suitable for	Perforex BC 1007 HS Perforex BC 1008 HS Perforex BC 2014 HS Perforex MT 2101 Perforex MT 2101 S Perforex MT 2201 Perforex MT 2201 S
Mere vpenjalnih ohišij maks.	Širina: 200 mm Višina: 300 mm Globina: 300 mm
Mere vpenjalnih ohišij min.	Širina: 90 mm Višina: 70 mm Globina: 70 mm

Features

Paketi	1 pc(s).
Neto teža	25 kg
Bruto teža	25 kg
Carinska tarifna številka	84669360
ETIM 9	EC003010
ETIM 8	EC003010
ECLASS 8.0	36609190
Opis izdelka	AS Multiple fastening, BC 1007/1008/2014, Clamping frame for several small enclosures, - 4 clamping positions in the frame, - Pneumatic clamping device, - Min. enclosure dimensions (W x H x D): 90 x 70 x 70 mm