


Rittal – The System.

Faster – better – everywhere.



AS 4050.318

Možnost rezanja navojev

State: 4.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.318 - Možnost rezanja navojev za Perforex LC 3030

Možnost rezanja navojev za laserski center Perforex LC, vključno z navojnimi rezalniki in vpenjalnimi čeljustmi za M3–M10.



Features

Št. Modela	AS 4050.318
Zasnova	Premični magazin za orodje s 6 položaji za magazine Držalo orodja Dodatna pogonska enota
Opis izdelka	Možnost rezanja navojev za ustvarjanje navojnih lukenj s Perforex Lasercenter LC.
Prednosti	Možna je obdelava projektov z navojnimi luknjami Hiter, samodejni preklop iz laserske funkcije v funkcijo rezanja navojev z namestitvijo dodatne strojne glave
Obseg dobave	Rezalnik navojev Vpenjalne enote za M3 – M10
Obdelovalna višina (maks.)	600 mm
Debelina materiala	5 mm
Za model št.	4050330
Paketi	1 pc(s).
Neto teža	78 kg
Bruto teža	78 kg
Carinska tarifna številka	84669360

Features

ECLASS 8.0

36600890

Opis izdelka

AS Tapping unit LC 3015/3030, Tapping option for Perforex Lasercenter LC, - Including equipped Tool holders M3 - M10., - Tool magazine with 6 slots., - SK30 Tool holder.